



Crossed Roller Bearing

RAU slim thin section crossed roller bearing-




Shaft diameter	80
Model No.	RAU8005
Main dimensions	
Inner diameter	80
Outer diameter	91
Roller pitch circle diameter	84.7
Width	5
Greasing hole d_0	1
r_{min}	0.15
Shoulder dimensions	
$d_s(max)$	82.5
$D_h (min)$	87
Basic load rating	
C kN	3.05
C0 kN	5.43
Mass	50
g	

Micro Cross-Roller Ring RAU

● Model composition

Model Number Coding



Considerations for model RAU (Small-diameter thin type. Width: 5mm)


Seals are not available. The only radial clearance available is C0.* The only accuracy available is normal grade (grade 0).

For a compact and lightweight system

□ Micro Cross-Roller Ring with inner diameter of 10 mm and outer diameter of 21 mm

□ More compact than a conventional angular contact ball bearing

□ Spacer retainer enables smooth movement and high rotation accuracy.



Structure

In the RAU, the rollers travel on the V-shaped raceways ground into the inner and outer rings.

Alternating rollers are arrayed orthogonally so that one bearing can support loads and moments in any direction.


Also, because of the integrated structure, the RAU can be used for either inner ring or outer ring rotation.

Fig. 1 Structure of Cross Roller-Ring Model RAU


1. Compact and Rigid

The RAU is more compact and lighter weight than a double row angular contact ball bearing. It is also more rigid, even though it is made as compact as possible.

●Comparison, 50 mm inner diameter



Moment Rigidity Comparison



Comparison of cross-sectional area and mass


Model No.	RAU5005	7910 (DB)
Cross-sectional area	27.5mm ²	264mm ²
Mass	32g	260g

2. Light Weight

The cross-sectional area of the model RAU is 57% smaller than the Cross-Roller Ring model RA, which was previously the thinnest ever. This enables further weight reduction. The line-up also includes other models

whose inner diameters are the smallest to date: 10, 15, 20, 30, and 40mm.

●Comparison of cross section and mass, 50 mm inner diameter



Model No.	RAU5005	RA5008
Cross-sectional area	27.5mm ²	64mm ²
Mass	32g	80g

Accuracy standards

Rotational accuracy

- Rotational Accuracy of the Inner Ring Unit: μm - Rotational Accuracy of the Outer Ring Unit: μm

Nominal dimension of bearing inner diameter (d) (mm)		Radial runout tolerance of inner ring				Axial runout tolerance of inner ring				Nominal dimension of bearing outer diameter (D) (mm)		Radial runout tolerance of outer ring			Axial runout tolerance of outer ring		
Above	Or less	Grade 0	Grade P6	Grade P5	Grade P4	Grade 0	Grade P6	Grade P5	Grade P4	Above	Or less	Grade 0	Grade P5	Grade P4	Grade P6	Grade P5	Grade P4
--	18	10	--	--	--	10	--	--	--	--	65	13	--	--	13	--	--
18	40	13	--	--	--	13	--	--	--	65	80	13	8	5	13	8	5
40	65	13	10	5	4	13	10	5	4	80	100	15	10	6	15	10	6
65	80	15	10	5	4	15	10	5	4	100	120	15	10	6	15	10	6
80	100	15	13	6	5	15	13	6	5	120	140	20	11	7	20	11	7
100	120	20	13	6	5	20	13	6	5	140	180	25	11	7	25	11	7
120	140	25	18	8	6	25	18	8	6	180	200	25	15	10	25	15	10
140	180	25	18	8	6	25	18	8	6	200	250	30	15	10	30	15	10
180	200	30	20	10	8	30	20	10	8								

- The rotational accuracy of model RAU (Small-diameter thin type, Width: 5mm) is only available in normal grade (grade 0).

Dimensional accuracy

Unit: μm

Basic dimension d, D [mm]		Bearing inner diameter: Dimensional tolerance of dm		Bearing outer diameter: Dimensional tolerance of Dm		Bearing width: Dimensional tolerance of B, B1			
Above	Or less	Upper limit	Lower limit	Upper limit	Lower limit	Upper limit	Lower limit	Upper limit	Lower limit
--	18	0	-8	--	--	0	-120		
18	30	0	-10	0	-9	0	-120		
30	50	0	-12	0	-11	0	-120		
50	80	0	-15	0	-13	0	-120		
80	120	0	-20	0	-15	0	-120		
120	150	0	-25	0	-18	0	-120		
150	180	0	-25	0	-25	0	-120		
180	250	0	-30	0	-30	0	-120		

- dm and Dm represent the arithmetic averages of the maximum and minimum diameters obtained by measuring the inner and outer diameters of the bearing at two points.

Radial clearance standard

Unit: μm

Roller Pitch circle diameter (dp) [mm]		CC0		C0	
Above	Or less	Min.	Max.	Min.	Max.
--	18	--	--	0	15
18	30	--	--	0	15
30	50	--	--	0	15
50	80	-8	0	0	15
80	120	-8	0	0	15
120	140	-8	0	0	15
140	160	-8	0	0	15
160	180	-10	0	0	20
180	200	-10	0	0	20
200	225	-10	0	0	20